


Lens Dimensions (units in mm)



Specifications

Lens Information

|              |            |
|--------------|------------|
| Focal Length | 16 mm      |
| Aperture     | F2.8 ~ F16 |
| Lens D-FOV   | 31.0°      |
| Lens H-FOV   | 27.5°      |
| Lens V-FOV   | 15.7°      |
| TTL          | 55.00 mm   |
| BFL          | 13.10 mm   |
| MOD          | 0.1 m      |
| Distortion   | < 0.5%     |
| Image Size   | 2/3"       |
| Resolution   | 8MP        |

Environmental and Mechanical

|                            |                  |
|----------------------------|------------------|
| Lens Operating Temperature | - 20° to +100°C  |
| Weight                     | 63 grams         |
| Material                   | Metal            |
| Operation Focal            | Manual With Lock |
| Operation Zoom             | Fixed            |
| Operation Iris             | Manual With Lock |
| Mount Type                 | C - Mount        |

Order Information

| Part Number | Description   |
|-------------|---|
| C11808160FF | C-Mount Lens 16mm Fixed Focal Length<br>Aperture Range From F2.8 ~ F16<br>Up To 8 Megapixel Resolution. |



Compatible With C-Mount Cameras