


Lens Dimensions (units in mm)



Specifications

Lens Information

| | |
|--------------|--------------|
| Focal Length | 16 mm |
| Aperture | F1.4 ~ Close |
| Lens D-FOV | 38.0° |
| Lens H-FOV | 32.5° |
| Lens V-FOV | 18.5° |
| TTL | 73.18 mm |
| BFL | 12.73 mm |
| MOD | 0.2 m |
| Distortion | < - 1.0% |
| Image Size | 2/3" |
| Resolution | 5MP |

Environmental and Mechanical

| | |
|----------------------------|------------------|
| Lens Operating Temperature | - 20° to +100°C |
| Weight | 175 grams |
| Material | Metal |
| Operation Focal | Manual With Lock |
| Operation Zoom | Fixed |
| Operation Iris | Manual With Lock |
| Mount Type | C - Mount |

Order Information

| Part Number | Description |
|-------------|---|
| C2305160FF | C-Mount Lens 16mm Fixed Focal Length Aperture Range From F1.4 ~ Close Up To 5 Megapixel Resolution. |



Compatible With C-Mount Cameras