


Lens Dimensions (units in mm)



Specifications

Camera Information

Focal Length	8 mm
Aperture	F1.4
Lens D-FOV	67.1°
Lens H-FOV	56.3°
Lens V-FOV	43.7°
TTL	57.53 mm
MBFL	9.73 mm
MOD	0.1 m
TV Distortion	1.0%
Image Size	2/3"
Resolution	5MP
Focusing Range (m)	0.1~∞
Shooting Range at MO.D.	110 mm x 82.5 mm
Filter Thread	M37×P0.5 mm

Environmental and Mechanical

Operating Temperature	20°C to +60°C
Size	$\varnothing 39.3 \times 47.8$ mm
Weight	108 grams
Material	Metal
Operation Focal	Manual with Lock
Operation Zoom	Fixed
Operation Iris	Manual with Lock
Mount Type	C-Mount

Order Information

Part Number	Description
C2305080FF	C-Mount Lens 8mm Fixed Focal Length Aperture Range From F1.4 Up To 5 Megapixel Resolution



Compatible With C-Mount Cameras