


Lens Dimensions (units in mm)



Specifications

Camera Information

Focal Length	16 mm
Aperture	F1.4
Lens D-FOV	37.3°
Lens H-FOV	30.3°
Lens V-FOV	23°
TTL	49.03 mm
MBFL	12.43 mm
MOD	0.1 m
TV Distortion	0.10%
Image Size	2/3"
Resolution	5MP
Focusing Range (m)	0.1~∞
Shooting Range at MO.D.	55 mm x 41.25 mm
Filter Thread	M30.5×P0.5 mm

Environmental and Mechanical

Operating Temperature	20°C to +60°C
Size	Ø33.5×36.6 mm
Weight	61 grams
Material	Metal
Operation Focal	Manual with Lock
Operation Zoom	Fixed
Operation Iris	Manual with Lock
Mount Type	C-Mount

Order Information

Part Number	Description
C2305500FF	C-Mount Lens 16mm Fixed Focal Length Aperture Range From F1.4 ~ Close Up To 5 Megapixel Resolution



Compatible With C-Mount Cameras