


OSM-SL2610 OEM



- Synaptics Astra™ SL2610 SOC
- Cortex-A55 up-to 2Ghz
- Google Kelvin Core AI / NPU 1 TOPS
- Up to 2GB LPDDR4 memory
- Support PSA Level 3 Security
- OSM-S formfactor



	Entry	Mid-Range	Performance
Processor	SL2613	SL2617	SL2619
	Single Core A55 @ 1.2 GHz	Dual Core A55 @ 1.7 GHz	Dual Core A55 @ 2 GHz
Memory	512MB DDR3L	1GB LPDDR4	2GB LPDDR4
eMMC	32GB	32GB	64GB
NPU / AI	-	✓	✓
GPU	-	✓	✓
Camera	-	✓	✓
Ethernet	1xGbE	1xGbE	2xGbE
PSA	L2	L2	L3

TechNexion
INNOVATORS OF TECHNOLOGY



For more information:

🏠 www.technexion.com

✉ sales@technexion.com

Get Started Today

