

TEP-0700-IMX6UL



- The TEP-0700-IMX6UL is a cost-optimized general industrial applications HMI based on an NXP i.MX6UL core Cortex-A7™ processor.
- The TEP-0700-IMX6UL features a 7-inch widescreen ratio multitouch PCAP touch screen with LED backlight and brushed aluminum front bezel.
- 4 RS-232, 2 CAN, 12 GPIO, 2 Fast Ethernet and USB interfaces
- Orderable with single voltage 12VDC, wide voltage 9 - 36VDC or 802.3at PoE (power over ethernet) options.
- Linux and Yocto runtime images and full source code available.

Specifications



yocto
PROJECT

Core System

Processor	NXP i.MX6 UL
Processor Speed	528MHz
Architecture	ARM Cortex-A7
PMIC	NXP PF3000
Memory	Up to 1GB DDR3L
Storage	eMMC (4GB Default)

Connectivity

Network LAN	2x Micrel KSZ8081RNBCA Fast Ethernet LAN
Power over Ethernet	PoE function 802.3at (optional)

External Connectors

Network	2x RJ45
USB	1x USB 2.0 Host 1x USB 2.0 OTG (Type-C)
CAN Bus	2x Flex CAN version 2.0B compliant
Serial	4x RS-232
GPIO	12x GPIO
Buttons	1x Boot Select 1x Reset
Indicators	1x Programmable LED
SD Cardslot	1x MicroSD Card slot

Display

LCD	7 inch widescreen LCD with LED backlight
Resolution	800 x 480 pixels
Luminance	350 cd/m ²
Maximum Colors	16.7 million
Touchscreen	Projective Capacitive (multitouch)

Power Specifications


Power Input	Available with 12V 9-36V (wide power input)
Power Over Ethernet	PoE function 802.3at (optional)
Power Connector	2-pin Micro-Fit 3.0
Power Consumption	Depending on Configuration

Operation Systems

Standard Support	Linux Yocto
Extended Support	Commercial Linux

Dimensions

(units in mm)



Environmental and Mechanical

Enclosure Material	Metal
Front Bezel	Brushed Anodized Aluminium
IP Rating	IP65 Front
Dimensions	198 (W) x 136 (H) x 50 (D) mm
Weight	945 grams
Temperature	Commercial: 0° to +50°C
Relative Humidity	10 to 90 %
MTBF	50 000 Hours
Shock	15G half-sine 11 ms duration
Vibration	1 Grms random 5-500Hz hr/axis
Certification	Compliant with CE / FCC / RoHS / REACH directives

Modular Expansion Options

Power Expansion Module	TXR-P1-12V-LAN1 (12V 3A) TXR-P1-1030V-LAN1 (9-36V 5A) TXR-P1-12V-POE1 (12V 3A) or (PoE 802.3at)
------------------------	---

Mounting Options

VESA Mounting	35*75 VESA MIS C. Standard (separate purchase)
Surface Mounting	8 mounting holes

Ordering Information

TEP0700-IMX6Gx-05-Rxx-Exx-Lxxx-xxxx

	Code	Description
Processor	IMX6G	NXP i.MX6UltraLite
Processor Speed	05	528MHz
Memory	R05	512MB DDR3L
Storage	E04	eMMC capacity E04 = 4GB / E16 = 16GB / E32 = 32GB / E64 = 64GB
Power Expansion	L112	TXR-P1-12V-LAN1 (12V 3A)
	L130	TXR-P1-1030V-LAN1 (9-36V 5A)
	LPOE	TXR-P1-12V-POE1 (12V 3A) or (PoE 802.3at)
Custom ID	XXXX	Custom Part number ID for customized Software loader and special component (BOM)