

TC-0700

- TC-0700 is an ultra-slim, low power, fanless HMI based on a Solo or DualLite core ARM Cortex-A9 NXP i.MX6 processor.
- 7 inch Projective Capacitive (multitouch) high resolution (1024 x 600) bright (500 nits) widescreen LCD with LED backlight.
- Galvanic isolated CAN Bus and Serial (RS-232/422/485) ports.
- USB 2.0 Host, USB 2.0 OTG, microSD card slot, 4x GPIO (galvanic isolated) and HDMI for secondary display.
- PoE function 802.3at or 9-36V DC power input.
- Available with colorful bezels.



Specifications

Core System

Processor	NXP i.MX6 Solo NXP i.MX6 DualLite
Architecture	ARM Cortex-A9
PMIC	NXP MMPF0100
Memory	Up to 2GB DDR3
Storage	4GB eMMC

Connectivity

Network LAN	1x Atheros AR8035 Gigabit LAN
Power over Ethernet	PoE function 802.3at (optional)

Video

GPU Engine	Vivante GC320 (2D Composition) Vivante GC880 (Solo/DualLite)
Video Decode	1080p30 + D1 (Solo/DualLite)
Video Encode	BP/Dual 720p

Audio

Audio Codec	NXP SGTL5000
Speaker	Internal audio speaker connector (stereo) (2W pre-amplified)

Power Specifications

Power Input	10-30+V DC
Power Connector	2-pin Micro-Fit 3.0
Power Consumption	Depending on Configuration

Operating Systems

Standard Support	Linux Yocto Android Ubuntu
Extended Support	Commercial Linux

Environmental and Mechanical

Enclosure Material	Metal
Front Bezel	Colorful Plastic Frame
Dimensions	184.3(W)x122.1(H)x29.6(D) mm
Relative Humidity	10 to 90 %
MTBF	50,000 Hours
Shock	15G half-sine 11 ms duration
Operation Temperature	Commercial: 0° to +50°C
Vibration	1 Grms random 5-500Hz hr/axis
Weight	595 grams

Mounting Options

Rear Mounting	6 mounting clips required (included)
VESA Mounting	35*75 VESA MIS-C Standard (separate purchase)

Display

LCD	7 inch widescreen LCD with LED backlight
Resolution	1024 x 600 pixels
Luminance	500 cd/m ²
Maximum Colors	16.7 million
Touchscreen	Projective Capacitive (multitouch)


External Connectors

External Display	1x HDMI
Network	1 x RJ45
USB	1 x USB 2.0 Host 1 x USB 2.0 OTG
CAN Bus	2 x Flex CAN version 2.0B compliant (galvanic isolated)
Serial	1 x RS-232 (galvanic isolated) 1 x RS-232/422/485 (galvanic isolated)
GPIO	4 x GPIO (galvanic isolated)
Buttons	1 x Boot Select 1 x Reset
SD Cardslot	1 x MicroSD Card slot


Certification and Compliance

Certification	Compliant with CE / FCC / RoHS / REACH directives
---------------	---

Dimensions (units in mm)



Block Diagram



Order Information

TC0700-P-IMX6x-Rxx-Exx-xx-xxxx-xxxx

	Code	Description
Processor	IMX6S	NXP i.MX6 Solo
	IMX6U	NXP i.MX6 DualLite
Memory	R05	512MHz DDR3L
	R10	1GB DDR3L
Storage	E04	eMMC capacity E04 = 4GB / E16 = 16GB / E32 = 32GB / E64 = 64GB
Power Expansion	BK	Black Frame
	BL	Blue Frame
	GN	Green Frame
	GY	Grey Frame
	OR	Orange Frame
	RD	Red Frame
	WT	Ivory White Frame
	YL	Yellow Frame
Custom ID	XXXX	Custom Part number ID for customized Software loader and special component (BOM)