

VLS3-AR0822-SL

- onsemi AR0822 8MP Rolling Shutter Sensor
- 4K HDR Imaging Capabilities
- Near Infra-Red Enhancement for Outdoor Applications
- Designed for Low Light Applications
- S-Mount for Interchangeable Lenses
- FAKRA Automotive Connector
- Plug & Play with Linux OS & Yocto
- Comes with VizionViewer™ Configuration Utility and VizionSDK



Specifications

Camera Information

CMOS Sensor	onsemi AR0822
Active Pixels	3848 (H) x 2168 (V) = 8MP
Pixel Size	2.0 μm x 2.0 μm
Optical Format	1/2" (Diagonal 8.81 mm)
Shutter Type	Rolling Shutter
Chromaticity	Color
Illuminated type	Back Side Illuminated (BSI)
Maximum Frame Rate (UYVY)	3840 x 2160 @ 15 fps 2560 x 1440 @ 30 fps 1920 x 1080 @ 60 fps 1280 x 720 @ 60 fps 640 x 480 @ 60 fps
Maximum S/N Ratio	40.5 dB
HDR Support	Yes
Output Format	UYVY

Camera Interface

Connector	FAKRA SMB Jack Z-Code
Serial Link	FPD-Link III

Power

Supply Voltage	12V $\pm$ 5%
Power Consumption	UYVY 3840 x 2160 @ 15 fps $\leq$ 1.3W
Standby Power	$\leq$ 0.1W Standby



yocto
PROJECT

Software Support

Platform Support	x86 Intel / AMD NXP i.MX8M Mini / Plus NXP i.MX93 TI Sitara™ AM62x / AM62A TI Jacinto™ TDA4VM / TDA4VA / TDA4VH NVIDIA Jetson Nano NVIDIA Xavier NX NVIDIA Orin Nano/NX
Operation System	Linux Yocto
Software	VizionViewer™
Development SDK	VizionSDK


Environmental and Mechanical

Dimensions	29.5(W) x 29.5(H) x 32.2(D) mm
Weight	45 grams
Relative Humidity	10 to 90 %
MTBF	50,000 Hours
Shock	15G half-sine 11 ms duration
Operating Temperature	-30°C to +70°C
Vibration	1 Grms random 5-500Hz hr/axis


Certification and Compliance

Certification	Compliant with CE / FCC / RoHS / REACH directives
---------------	---


Spectral Characteristics



Block Diagram



Dimensions (units in mm)



Order Information

VLS3-AR0822-x-Sxx-xx

Part Number Rules

Option	Code	Description
Chromaticity	C	Color
Lens	S42	S-Mount Module D-FOV 42°
	S72	S-Mount Module D-FOV 72°
	S108	S-Mount Module D-FOV 108°
	S150	S-Mount Module D-FOV 150°
Filter	-	-
	IR	IR Cut Filter 650nm

For further customization or questions about orders, contact your TechNexion sales representative.

Optional Accessories

300-MOUNT-BRACKET

An easy to attach A-Mount bracket for TechNexion 30mm enclosed cameras.



300-MOUNT-BRACKET



300-MOUNT-BRACKET on tripod
(tripod not included)

TechNexion
INNOVATORS OF TECHNOLOGY

For more information:

www.technexion.com

sales@technexion.com

Lens Information

				
	VLS3-AR0822-C-S42-IR	VLS3-AR0822-C-S72-IR	VLS3-AR0822-C-S108-IR	VLS3-AR0822-C-S150-IR
Focus Type	Fixed Focus	Fixed Focus	Fixed Focus	Fixed Focus
Focal Length	12 mm	6 mm	5 mm	3.2 mm
Aperture	F2.0	F2.8	F2.0	F2.0
Lens D-FOV	41.0°	72.0°	113.0°	160.0°
Lens H-FOV	38.0°	61.0°	94.0°	131.0°
Lens V-FOV	22.0°	47.0°	50.0°	99.0°
Module D-FOV	41.7° ± 5%	72.0° ± 5%	108.3° ± 5%	150.0° ± 5%
Module H-FOV	36.3° ± 5%	64.7° ± 5%	93.0° ± 5%	132.6° ± 5%
Module V-FOV	20.5° ± 5%	39.0° ± 5%	50.6° ± 5%	77.6° ± 5%
TTL	23.9 mm	28.6 mm	29.4 mm	44.98 mm
BFL	3.88 mm	8.8 mm	6.05 mm	6.14 mm
MOD	0.15 m	0.1 m	0.3 m	0.3 m
Distortion	<0.2%	<0.5%	<-43.70%	<-32%
IR-Filter	650 nm	650 nm	650 nm	650 nm

FPD-Link III Frame Grabbers

Adding TechNexion FPD-Link III cameras to an existing x86 Intel or AMD based system couldn't be easier by using our full range frame grabber cards.

- Available in 1 / 2 / 4 / 8 port FPD-Link III camera frame grabber configuration
- Fits in a standard PCI Express Gen 3 slot
- Plug-n-Play driver-less UVC based solution
- Complete Fanless design with brushed aluminium thermal solution
- Comes with TechNexion VizionSDK




UVC-VL-3100



PCIE-VL-3120



PCIE-VL-3440



PCIE-VL-3480

Nvidia Orin Fanless AI Computing



- Nvidia Orin Nano / NX Systems
- Up-to 8 FPD-Link III cameras
- Nvidia Jetpack driver integration
- TechNexion VizionSDK

TRAQ-4VM Robotic AMR Solutions



- TI TDA4VM
- Up-to 8 FPD-Link III cameras
- FPD-Link III Display
- Single Pair Ethernet (SPE) sensor network extension
- Linux / Debian support
- TechNexion VizionSDK

i.MX8M Plus HMI Solutions



- NXP i.MX8M Plus
- Available as 15" / 15.6" / 21.5" Display solution
- Up-to 2 FPD-Link III cameras
- FPD-Link III remote Display
- Linux / Debian / Android support
- TechNexion VizionSDK

i.MX8M Plus Edge Computing



- NXP i.MX8M Plus
- Available with By-pass Ethernet solution
- Extensive low-speed I/O availability
 - GPIO / UART / CAN / USB
- Up-to 2 FPD-Link III cameras
- Linux / Debian / Android support
- TechNexion VizionSDK