


TEVS-AR0144

- Onsemi AR0144 1MP global shutter image sensor with ISP.
- Captures high-speed dynamic targets clearly within an ultra-short exposure time.
- Convenient S-Mount (M12) interchangeable lens.
- Driver integration support for :
 - NXP i.MX8 / i.MX9 Family
 - Nvidia Jetson Nano / Xavier NX / Orin
 - TI Sitara™ AM62x / Jacinto™ TDA4 Family
- Comes with VizionViewer™ Configuration Utility and VizionSDK



Camera Information

CMOS Sensor	onsemi AR0144
Active Pixels	1280 (H) x 800 (V) = 1 MP
Pixel Size	3.0 μm x 3.0 μm
Optical Format	1/4" (Diagonal 4.5 mm)
Shutter Type	Global Shutter
Chromaticity	Color
Illuminated Type	Front Side Illuminated (FSI)
Maximum Frame Rate (UYVY)	1280 x 800 @ 60 fps 1280 x 720 @ 60 fps 640 x 480 @ 60 fps
Maximum S/N Ratio	38 dB
Input Clock Range	48 MHz
Output Format	UYVY

Camera Interface

Module Data Transmission	MIPI CSI-2, up to 4 lanes
Communication Interface	I ² C
Connector	70 Pin Standardized Connector

Power

Supply Voltage	I/O: 1.8V Analog: 2.8V Digital: 1.15V & 3.3V
Power Consumption	1280 x 800 @ 60 fps $\leq$ 486 mW
SW Standby Power (Total)	$\leq$ 46 mW Standby
HW Standby Power (Total)	$\leq$ 21 mW Standby

Software Support

Platform Support	NXP i.MX8M Nano / Mini / Plus NXP i.MX93 / i.MX95 TI Sitara™ AM62 / AM62A / AM67 TI Jacinto™ TDA4VM / AM68 TI Jacinto™ TDA4VH / AM69 NVIDIA Jetson Nano NVIDIA Xavier NX NVIDIA Orin Nano / NX Intel Alder Lake-N RENESAS RZ / V2H / V2N ST STM32MP25 BeagleY®-AI / BeaglePlay® Raspberry Pi 4 / Raspberry Pi 5
Operation System	Linux Yocto Android
Software	VizionViewer™
Development SDK	VizionSDK


Environmental and Mechanical

Dimensions	24.5(W) x 24.5(H) x 3.47(D) mm
Weight	$\leq$ 3 grams
Operating Temperature	- 30°C to + 70°C


Certification and Compliance

Certification	Compliant with CE / FCC / RoHS / REACH directives
---------------	---


Spectral Characteristics




Block Diagram



Dimensions (units in mm)





Connector Pin Definition



DF40C-70DP-0.4V(51)

No.	Pin Define	Level	No.	Pin Define	Level
01	3V3D	3.3V	02	3V3D	3.3V
03	3V3D	3.3V	04	3V3D	3.3V
05	GND	GND	06	GND	GND
07	NC		08	NC	
09	GND	GND	10	GND	GND
11	2V8A	2.8V	12	2V8A	2.8V
13	GND	GND	14	GND	GND
15	1V8D	1.8V	16	1V8D	1.8V
17	GND	GND	18	GND	GND
19	1V15D	1.15V	20	1V15D	1.15V
21	GND	GND	22	GND	GND
23	NC		24	NC	
25	NC		26	NC	
27	NC		28	NC	
29	NC		30	NC	
31	NC		32	NC	
33	MCU_INT_1V8_N	1.8V	34	NC	
35	GND	GND	36	GND	GND
37	H_CAM_DN0		38	CSI_FRAME_SYNC	1.8V
39	H_CAM_DP0		40	CSI_nRST	1.8V
41	GND	GND	42	GND	GND
43	H_CAM_DN1		44	NC	1.8V
45	H_CAM_DP1		46	CSI_FLASH_OUT	1.8V
47	GND	GND	48	GND	GND
49	H_CAM_DN2		50	STANDBY	1.8V
51	H_CAM_DP2		52	CSI_SHUTTER	1.8V
53	GND	GND	54	GND	GND
55	H_CAM_DN3		56	H_I2C_SCL	1.8V
57	H_CAM_DP3		58	H_I2C_SDA	1.8V
59	GND	GND	60	GND	GND
61	H_CAM_CKN		62	NC	
63	H_CAM_CKP		64	NC	
65	GND	GND	66	NC	
67	NC		68	NC	
69	GND	GND	70	GND	GND

Lens Information

		
	TEVS-AR0144-C-S33-IR	TEVS-AR0144-C-S83-IR
Focus Type	Fixed Focus	Fixed Focus
Focal Length	8 mm	2.85 mm
Aperture	F1.8	F2.8
Module D-FOV	33.1° ± 5%	82.6° ± 5%
Module H-FOV	28.0° ± 5%	73.5° ± 5%
Module V-FOV	17.4° ± 5%	50.3° ± 5%
TTL	26.2 mm	20 mm
BFL	7.8 mm	2.03 mm
MOD	0.3 m	0.3 m
Distortion	<-5.03%	<-0.35%
IR-Filter	650 nm	650 nm

Order Information


TEVS-AR0144-x-Sxx-xx-xxx-xxxx

Option	Code	Description
Chromaticity	C	Color
Lens	S33	S-Mount Module D-FOV 33°
	S83	S-Mount Module D-FOV 83°
Filter	-	-
	IR	IR Cut Filter 650nm
Evaluation Kit	-	70 pin Standardized Camera Connector
	EVK	70 pin Standardized Camera Connector with FPC cable
	RPI15	15 pin Standardized ZIF Connector with FFC cable
	RPI22	22 pin Standardized ZIF Connector with FFC cable
	NXP	Mini-SAS connection cable for NXP Evaluation Board
Custom ID	XXXX	Custom Part number ID for customized Software loader and special component (BOM)

For customization, please contact your TechNexion sales representative.

TEVS-AR0144-x-Sxx-IR-EVK


onsemi AR0144 1MP global shutter with ISP camera module + S-Mount (M12) lens with IR-cut filter + FPC connection cable for TechNexion SOM EVK



Package Content


- TEVS-AR0144
- S-Mount lens
- 20cm flexible PCB for TechNexion EVK

TechNexion
INNOVATORS OF TECHNOLOGY



TEVS-AR0144-x-Sxx-IR-RPI15


onsemi AR0144 1MP global shutter with ISP camera module + S-Mount (M12) lens with IR-cut filter + RPI 15 Pin converter and FFC



Package Content

- TEVS-AR0144
- S-Mount lens
- RPI 15 Pin compatible converter PCB
- 20cm 15 Pin FPC cable

**TEXAS
INSTRUMENTS**



SK-TDA4VM


NVIDIA



JETSON NANO
XAVIER NX

TEVS-AR0144-x-Sxx-IR-RPI22

onsemi AR0144 1MP global shutter with ISP camera module + S-Mount (M12) lens with IR-cut filter + RPI 22 Pin converter and FFC



Package Content

- TEVS-AR0144
- S-Mount lens
- RPI 22 Pin compatible converter PCB
- 10cm 22 Pin FPC cable

NVIDIA




ORIN NANO
ORIN NX

**TEXAS
INSTRUMENTS**



SK-AM62A


NXP



NXP i.MX93 EVK

TEVS-AR0144-x-Sxx-IR-NXP

onsemi AR0144 1MP global shutter with ISP camera module + S-Mount (M12) lens with IR-cut filter + Mini-SAS Connection Cable for NXP i.MX8 Evaluation Board



Package Content

- TEVS-AR0144
- S-Mount lens
- 20cm Mini-SAS cable for NXP i.MX8 Family EVK

NXP

NXP i.MX8M MINI EVK
NXP i.MX8M NANO EVK
NXP i.MX8M PLUS EVK



TechNexion
INNOVATORS OF TECHNOLOGY

For more information:
www.technexion.com
sales@technexion.com