


UVLS-FPD3-AR0144

- onsemi AR0144 1MP Global Shutter Sensor
- Captures high-speed dynamic targets clearly within an ultra-short exposure time.
- S-Mount for Interchangeable Lenses
- FAKRA Z-Code Automotive Connector
- Plug & Play with Linux OS & Yocto
- VizionViewer™ configuration utility
- VizionSDK for custom development



Camera Information

CMOS Sensor	onsemi AR0144
Active Pixels	1280 (H) x 800 (V) = 1 MP
Pixel Size	3.0 μ m x 3.0 μ m
Illuminated Type	Front Side Illuminated (FSI)
Maximum S/N Ratio	38 dB
Optical Format	1/4" (Diagonal 4.5 mm)
Shutter Type	Global Shutter
Chromaticity	Color
Maximum Frame Rate (YUV422-UYVY)	1280 x 800 @ 60 fps 1280 x 720 @ 60 fps 640 x 480 @ 60 fps
Output Format	YUV422-UYVY RGB888 / RGB565 RAW8 / RAW10 / RAW12

Camera Interface

Serial Link	FPD-Link III
Serializer	TI DS90UB953
Connector	FAKRA SMB Jack Z-Code

Power

Power over Coax	10.8V - 26.4V
Power Consumption	1280 x 800 @ 60 fps \leq 0.9W
Standby Power	\leq 0.1W Standby

Software Support

Platform Support	NVIDIA Jetson AGX Orin NVIDIA Jetson Orin Nano / NX NVIDIA Jetson Xavier NX NVIDIA Jetson Nano NXP i.MX95 TI Sitara™ AM68 / AM69 TI Jacinto™ TDA4VM / TDA4VH
Operation System	Linux Yocto
Software	VizionViewer™
Development SDK	VizionSDK



VizionSDK VizionViewer™


Environmental and Mechanical

Dimensions	24.5(W) x 24.5(H) x 30(D) mm
Weight	\leq 20 grams
Operating Temperature	-30°C to + 70°C


Certification and Compliance

Certification	Compliant with CE / FCC / RoHS / REACH directives
---------------	---------------------------------------------------


Spectral Characteristics



Block Diagram



Dimensions (units in mm)



Order Information

UVLS-FPD3-AR0144-x-Sxx-xx-xxxx

Option	Code	Description
Chromaticity	C	Color
Lens	S33	S-Mount Module D-FOV 33°
	S83	S-Mount Module D-FOV 83°
Filter	-	-
	IR	IR Cut Filter 650nm
Custom ID	xxxx	Custom Part number ID

For customization, please contact your TechNexion sales representative.

Optional Accessories

An easy to attach A-Mount bracket for TechNexion 30mm enclosed cameras.



245-MOUNT-BRACKET



245-MOUNT-BRACKET on tripod
(tripod not included)

Custom Lens Solutions

		
	UVLS-FPD3-AR0144-C-S33-IR	UVLS-FPD3-AR0144-C-S83-IR
Focus Type	Fixed Focus	Fixed Focus
Focal Length	8 mm	2.85 mm
Aperture	F1.8	F2.8
Module D-FOV	$33.1^\circ \pm 5\%$	$82.6^\circ \pm 5\%$
Module H-FOV	$28.0^\circ \pm 5\%$	$73.5^\circ \pm 5\%$
Module V-FOV	$17.4^\circ \pm 5\%$	$50.3^\circ \pm 5\%$
TTL	26.2 mm	20 mm
BFL	7.8 mm	2.03 mm
MOD	0.3 m	0.3 m
Distortion	<-0.03%	<-0.35%
IR-Filter	650 nm	650 nm
Lens Structure	6G + IR	2G + 3P + IR
First layer material	Glass	Plastic

FPD-Link III Frame Grabbers

The ease of usage, benefits and integration of a FPD-Link III camera in embedded systems is often made complex by the lack of FPD-Link ports and connectors on the system. For those scenarios TechNexion developed a framegrabber that easily plug into a USB port and extend the system with FPD-Link interconnect.



Up to 15m

Up to 15 meters of data and power transmission over a single COAX cable.



Software

Linux and Yocto systems are supported.



UVC Compliant

Fully plug-n-play in Windows and Linux embedded systems.



VizionViewer™

Easy to use software utility providing you with granular camera settings control.



Autodetect

Zero configuration required to detect any specific TechNexion FPD-Link camera by the framegrabber.



VizionSDK

Hardcode and control your cameras with C++ and Python code.

